

STREAK RETINOSCOPE

YZ24 CE

Streak Retinoscope

- The well positioned filament can be rotated for 360 ° and upward and downward moved Brightness of the streak can be adjusted.
- Quickly and precisely measure the astigmatism axis.
- The light can be converged, radiated and paralleled.
- Automatic turning off effectively protects the bulb.
- Two-steps adjustable brightness for bulb: S(Bright), W(Dark).



Specifications

Working Distance	1mm
Streak width	3mm - 20mm
Rotatable Angle	360°
Illumination Source	3V/2.1W , Halogen Bulb
Power Supply	AC110V/220V±10% , 50Hz/60Hz

YZ24B CE

Streak Retinoscope

- The filament can be 360 ° rotated and be adjusted upward and downward.
- Quickly and precisely measure the astigmatism axis.
- The light can be converged, radiated and paralleled.
- Continuously adjustable brightness.
- Convenient quick recharging.
- Anti-overcharging function protects the battery.
- Connected with the head of ophthalmoscope is also available.
- Double electricity double sufficient power. YZ24B and YZ11D could be recharged at the same time.



Specifications

Working Distance	0.67m
Streak width	3mm - 20mm
Illumination Source	3.5V/2.8W Halogen Bulb
Streak Rotation	360°
Power Supply	AC100V to 250V , 50Hz/60Hz
Power (Main Body of Ophthalmoscope)	Li+ battery pack DC:3.7V